




Eaton P580-015

DisplayPort Cable with Latching Connectors,
4K 60 Hz (M/M), Black, 15 ft. (4.57 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P580-015
UPC	037332145949
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.39 lb
WARRANTY	Limited lifetime
COMPLIANCES	WEEE Directive RoHS REACH

□□□□	
TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible MST Support Latching or Gripping Connector 3D Video Supported
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	DisplayPort Monitor Cable - 15-ft. (4.57 m)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Digital Video and Audio in one cable Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p Small footprint compared to VGA or DVI
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:2:2 4:2:0
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR3	DISPLAYPORT (MALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	DisplayPort
FEATURES	Flex Center
CONNECTOR GROUP	DisplayPort
CONNECTOR	DisplayPort (male)
CABLE LENGTH	15 Foot
CABLE OUTER DIAMETER	7.3 mm



(OD)	
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	73mm
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	14 - 20ft (4 - 6M)
