



Eaton P583-003

Mini DisplayPort to DisplayPort Adapter Cable, 4K 60Hz (M/M), DP Latching Connector, White, 3 ft. (0.9 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series adapter
CATALOG NUMBER	P583-003
UPC	037332174581
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.029 lb
COMPLIANCES	RoHS REACH WEEE Directive

TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	White
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	White
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	3D Video Supported Latching or Gripping Connector MST Support EDID Compatible
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	P583-003 Mini DisplayPort to DisplayPort 4K @ 60 Hz Adapter (M/M), 3-ft. (0.91 m)
PRODUCT HIGHLIGHTS	Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 4096 x 2160 @ 60Hz, including 1080p 3-ft. (0.91 m) Mini Displayport to Displayport Adapter Cable Connect your PC or Mac with Mini Displayport (or Thunderbolt) to a Displayport Monitor or TV Supports Displayport v1.2 Color: White
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:2:2 4:2:0
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR1	MINI DISPLAYPORT (MALE)
SIDEB CONNECTOR3	MINI DISPLAYPORT (MALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	DisplayPort
FEATURES	Flex Center

CONNECTOR GROUP	DisplayPort
CONNECTOR	Mini DisplayPort (male) DisplayPort (male)
CABLE LENGTH	3 Foot
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	48mm
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	Up to 4ft (up to 1M)



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

