




Eaton P583-006

Mini DisplayPort to DisplayPort Adapter
Cable, 4K 60Hz (M/M), DP Latching
Connector, White, 6 ft. (1.8 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series adapter
CATALOG NUMBER	P583-006
UPC	037332174598
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.2 lb
COMPLIANCES	RoHS REACH WEEE Directive

□□□□	
TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	White
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	White
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	Latching or Gripping Connector 3D Video Supported EDID Compatible MST Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	Mini DisplayPort to DisplayPort 4K @ 60 Hz Adapter (M/M), White, 6 ft. (1.8 m)
PRODUCT HIGHLIGHTS	Supports High Bit Rate 2 (HBR2) bandwidth up to 21.6 Gbps Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 60 Hz Gold-plated connectors and contacts for maximum conductivity Locking DisplayPort connector prevents accidental disconnection Meets DisplayPort 1.2 standards
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:2:2 4:2:0
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR1	MINI DISPLAYPORT (MALE)
SIDEB CONNECTOR3	MINI DISPLAYPORT (MALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	DisplayPort
FEATURES	Flex Center



CONNECTOR GROUP	DisplayPort
CONNECTOR	DisplayPort (male) Mini DisplayPort (male)
CABLE LENGTH	6 Foot
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	48mm
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
