



Eaton P584-006

Mini DisplayPort Cable, 4K 60Hz (M/M),
White, 6 ft. (1.8 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	P584-006
UPC	037332174628
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.11 lb
COMPLIANCES	RoHS WEEE Directive REACH

TYPE	Passive Cable
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	White
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	White
CONNECTOR PLATING	Gold
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible 3D Video Supported MST Support
CABLE JACKET MATERIAL	PVC
COLOR DEPTH	24-bit True color 24-bit True Color
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	6-ft. (1.83 m) Mini Displayport to Mini Displayport cable
PRODUCT HIGHLIGHTS	Connect your PC or Mac with Mini Displayport (or Thunderbolt) to a Mini Displayport Monitor or TV 6-ft. (1.83 m) Mini Displayport to Mini Displayport Cable Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p Supports Displayport v1.2
CONTACT PLATING	Gold
CHROMA SUB SAMPLING	4:2:0 4:2:2
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	MINI DISPLAYPORT (MALE)
SIDEB CONNECTOR1	MINI DISPLAYPORT (MALE)
SIDEB CONNECTOR3	MINI DISPLAYPORT (MALE)
DISPLAYPORT SPECIFICATION	1.2
TECHNOLOGY	DisplayPort
FEATURES	Flex Center
CONNECTOR GROUP	DisplayPort
CONNECTOR	Mini DisplayPort (male)
CABLE LENGTH	6 Foot

MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MINIMUM BEND RADIUS	48mm
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
CABLE TYPE	Passive
SIGNAL TRANSMISSION	Bidirectional
MAX RESOLUTION	4K/60
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
