



Eaton P686

Eaton Moeller series White moulded range (PREMERA) - Wiring Devices. RCD socket outlet, 13A, 2G, passive, 30mA

□□□□

PRODUCT NAME	Eaton Moeller series White moulded range (PREMERA) - Wiring devices
CATALOG NUMBER	P686
PRODUCT LENGTH/DEPTH	40 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	146 mm
PRODUCT WEIGHT	0.281 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN 61000-4-5 BS 7288 BS 1363-2 EN 61543



Powering Business Worldwide

□□□□

FEATURES	Antibacterial treatment Protective contact Halogen free
FITTED WITH:	Child-protection On/Off switch Fault current protection Loop through function
SURFACE FINISHING	Matt
SPECIAL FEATURES	Zinc Coated Steel with clear Passivation
TYPE	Premera White Moulded Sockets, passive 30mA
AMPERAGE RATING	13 A
VOLTAGE RATING	230 V AC (50/60 Hz)
CONTACT MATERIAL	Nickel Silver
HEAD STYLE	Combination head
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Thermoplastic
SWITCH TYPE	Double pole
MOUNTING METHOD	Flush mounted (plaster)
COLOR	White
FASTENING TYPE	Mounting with screw
CONNECTION TYPE	Screwed terminal
NUMBER OF GANGS	2
NUMBER OF SOCKET OUTLETS (SWITCHABLE)	2
NUMBER OF UNITS	1
RAL-NUMBER (AKIN)	0
RECOMMENDED BACK BOX DEPTH - MIN	25 mm
FIXING CENTERS	120.6 mm
BASE COLOR	White
BASE MATERIAL	Thermoplastic
SPECIAL POWER SUPPLY	No special power supply
TERMINAL MATERIAL	Brass
BUILT-IN INSTALLATION BOX DEPTH - MIN	25 mm
FAULT CURRENT RATING	250 mA
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
NOMINAL CURRENT	13 A
NOMINAL VOLTAGE -	240 V

□□

	eaton-british-standard-wiring-accessories-poster-en-uk.pdf
□□□□	eaton-premera-mix-specification-guide-product-aid-pa081001en-en-gb.pdf
□□□□	eaton-wiring-accessories-and-single-phase-distribution-pg00400018u-en-gb.pdf

