



Eaton P901

Eaton Moeller series White moulded range (PREMERA) - Wiring Devices. Cover plate, 1G, moulded, c/w earth strap

□□□□

PRODUCT NAME	Eaton Moeller series White moulded range (PREMERA) - Wiring devices
CATALOG NUMBER	P901
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	15 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.065 kg
COMPLIANCES	BS 5733 RoHS conform



Powering Business Worldwide

□□□□

FEATURES	Halogen free
FITTED WITH:	Mounting grid
SURFACE FINISHING	Matt
SPECIAL FEATURES	Terminal Screw Zinc Coated Steel with clear Passivation
TYPE	<ul style="list-style-type: none"> • Premera Mix module plates • Premera white moulded
VOLTAGE RATING	250 V AC
HEAD STYLE	Combination head
SURFACE PROTECTION	Untreated
COLOR	White
MATERIAL QUALITY	Thermoplastic
BASE COLOR	Gray
BASE MATERIAL	Thermoplastic
TERMINAL MATERIAL	Brass
BORE HOLE OPENING DIAMETER	0 mm
BUILT-IN HEIGHT	86 mm
BUILT-IN WIDTH	86 mm
NUMBER OF MODULES HORIZONTAL (MODULE SYSTEM)	1
NUMBER OF MODULES VERTICAL (MODULE SYSTEM)	0
NUMBER OF UNITS	1
NUMBER OF UNITS (HORIZONTAL)	1
NUMBER OF UNITS (VERTICAL)	1
RAL-NUMBER (AKIN)	9016
RECOMMENDED BACK BOX DEPTH - MIN	35 mm
FASTENING TYPE	Screw mounting
MOUNTING POSITION	Horizontal
NUMBER OF GANGS	1
FIXING CENTERS	60.3 mm
DEGREE OF PROTECTION	IP20
FRONT PLATE COLOR/FINISHING	White
FRONT PLATE DEPTH	9 mm

□□

	eaton-british-standard-wiring-accessories-poster-en-uk.pdf
□□□□	eaton-premera-mix-specification-guide-product-aid-pa081001en-en-gb.pdf
□□□□	eaton-wiring-accessories-and-single-phase-distribution-pg00400018u-en-gb.pdf

