

Eaton PDD22M0035VFFL

Eaton Power Defense 240V Max, Frame 2,
Two Pole, 35A, 100kA/240V, 50C Cal T-M
(Fxd-Fxd) TU, Std Term Load Only
(PDG2X2T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDD22M0035VFFL
UPC	786689248826
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	69.9 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	35 A
VOLTAGE RATING	240 V AC
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 UL/CSA Only
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	240Vac
SERIES	Power defense
TERMINALS	Standard Terminals Load Only
FRAME	2
CLASS	Class A
CALIBRATION	50C Calibration
RATING PLUG	no
INTERRUPT RATING	100 kAIC at 240 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	240 V
RATED OPERATIONAL CURRENT	35 A
NUMBER OF POLES	Two-pole

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

