

Eaton PDD22M0060TFFL

Eaton Power Defense molded case circuit breaker, UL/CSA 240V Max, Frame 2, Two Pole, 60A, 100kA/240V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X2T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDD22M0060TFFL
UPC	786687040064
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	69.9 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CSA

AMPERAGE RATING	60 A
VOLTAGE RATING	240 V AC
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 UL/CSA Only
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Load Only
FRAME	2
CLASS	Class A
INTERRUPT RATING	100 kAIC at 240 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	240
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	240 V
INTERRUPT RATING RANGE	22 kAIC Icu @250 Vdc 22 kAIC Icu @125 Vdc 100 kAIC @240V (UL)
NUMBER OF POLES	Two-pole

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

