



Eaton PDE33S0630SNNs

Eaton Moeller series Power Defense molded case switch-disconnector, 3p, 630A, frame size 3

□□□□

PRODUCT NAME	Eaton Moeller series Power Defense molded case switch-disconnector
CATALOG NUMBER	PDE33S0630SNNs
PRODUCT LENGTH/DEPTH	257 mm
PRODUCT HEIGHT	138 mm
PRODUCT WIDTH	138 mm
PRODUCT WEIGHT	6 kg
COMPLIANCES	RoHS conform

□□□□

□□

AMPERAGE RATING	630 A
VOLTAGE RATING	220 V - 440 V
MOUNTING METHOD	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	7.6 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
RATED OPERATING POWER AT AC-23, 400 V	0 kW
RATED OPERATING POWER AT AC-3, 400 V	0 kW
DEGREE OF PROTECTION (IP), FRONT SIDE	IP2X
NUMBER OF POLES	3
HANDLE COLOR	Black
NUMBER OF SWITCHES	1
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	0 kA
RATED OPERATING VOLTAGE (UE) AT AC - MAX	440 V
RATED PERMANENT CURRENT AT AC-21, 400 V	0 A
RATED PERMANENT CURRENT AT AC-23, 400 V	0 A
SWITCHING POWER AT 400 V	0 kW
HANDLE TYPE	Rocker lever
HOUSING COLOR	Gray
HOUSING MATERIAL	Plastic

