

Eaton PDF33F0400P2MJ

Power Defense Globally Rated 100% UL,
Frame 3, Three Pole, 400A, 25kA/480V,
PXR25 LSI w/ Modbus RTU and Relays, Std
Line Load Term (PDG3X3TA400)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDF33F0400P2MJ
UPC	786679399576
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.92 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked

AMPERAGE RATING	400 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T291
CIRCUIT BREAKER TYPE	PD3 Global (100% UL)
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	3
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	25 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	690
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	10 kAIC Icu @250 Vdc 35 kAIC @240V (UL)
NUMBER OF POLES	Three-pole
SPECIAL FEATURES	Modbus / relays

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

