



□□□□

Eaton PDF33M0250E4RJ

Power Defense Globally Rated 100% UL, Frame 3, Three Pole, 250A, 65kA/480V, PXR20 ARMS LSI w/ Relays, Std Line Load Term (PDG3X3TA350)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDF33M0250E4RJ
UPC	786679380512
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.92 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	250 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T284
CIRCUIT BREAKER TYPE	PD3 Global (100% UL)
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	3
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	690
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE

50 kAIC Icu/ 40 kAIC Ics/
 105 kAIC Icm @440V (IEC)
 22 kAIC Icu @250 Vdc
 100 kAIC Icu/ 100 kAIC Ics/
 220 kAIC Icm @240V (IEC)
 30 kAIC Icu/ 15 kAIC Ics/ 63
 kAIC Icm @525V South
 Africa (IEC)
 70 kAIC Icu/ 53 kAIC Ics/
 154 kAIC Icm @380-415V
 (IEC)
 15 kAIC Icu/ 7.5 kAIC Ics/
 31.5 kAIC Icm @690V (IEC)
 100 kAIC @240V (UL)
 65 kAIC @480V (UL)
 50 kAIC Icu/ 30 kAIC Ics/
 105 kAIC Icm @480V Brazil
 (IEC)
 35 kAIC @600V (UL/CSA)

NUMBER OF POLES	Three-pole
TRIP RATING	250 A
SPECIAL FEATURES	Relays

□□

