

Eaton PDF33MH400E5ML

Power Defense Globally Rated 100% UL,
Frame 3, Three Pole, 400A-High, 65kA/480V,
PXR20 ARMS LSIG w/ Modbus RTU and
Relays, Std Term Load Only
(PDG3X3TA401H)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDF33MH400E5ML
UPC	786679685464
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	138.9 mm
PRODUCT WEIGHT	5.92 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked

AMPERAGE RATING	400A High Override
VOLTAGE RATING	600 Vac
TRIP TYPE	T286
CIRCUIT BREAKER TYPE	PD3 Global (100% UL)
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Load Only
FRAME	3
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	690
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	22 kAIC Icu @250 Vdc 100 kAIC @240V (UL)
NUMBER OF POLES	Three-pole
TRIP RATING	400 A high override
SPECIAL FEATURES	Modbus / relays

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.

