



□□□□

Eaton PDF34F0125E2RN

Power Defense Globally Rated 100% UL,
Frame 3, Four Pole, 125A, 25kA/480V, PXR20
LSI w/ Relays, No Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDF34F0125E2RN
UPC	786679552315
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.68 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked IEC 60947-2



Powering Business Worldwide



AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T283
CIRCUIT BREAKER TYPE	PD3 Global (100% UL)
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	No Terminals
FRAME	3
CLASS	Class A
INTERRUPT RATING	25 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	690
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	35 kAIC @240V (UL) 18 kAIC Icu/ 5 kAIC Ics/ 37.8 kAIC Icm @525V South Africa (IEC) 25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @380-415V (IEC) 35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm @240V (IEC) 10 kAIC Icu @250 Vdc 25 kAIC @480V (UL) 20 kAIC Icu/ 20 kAIC Ics/ 42 kAIC Icm @480V Brazil (IEC) 14 kAIC @600V (UL/CSA) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @440V (IEC)
NUMBER OF POLES	Four-pole (100% N)
TRIP RATING	125 A
SPECIAL FEATURES	Relays

