



□□□□

## Eaton PDF34M0250E5XJ

Power Defense Globally Rated 100% UL, Frame 3, Four Pole, 250A, 65kA/480V, PXR20 ARMS LSIG w/ CAM Link, ZSI and Relays, Std Line Load Term (PDG3X4TA350)

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDF34M0250E5XJ
<b>UPC</b>	786679394267
<b>PRODUCT LENGTH/DEPTH</b>	109.1 mm
<b>PRODUCT HEIGHT</b>	257.1 mm
<b>PRODUCT WIDTH</b>	182.9 mm
<b>PRODUCT WEIGHT</b>	7.68 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60947-2 CCC Marked



Powering Business Worldwide



<b>AMPERAGE RATING</b>	250 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T286
<b>CIRCUIT BREAKER TYPE</b>	PD3 Global (100% UL)
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>PROTECTION</b>	100% neutral protection
<b>TERMINALS</b>	Standard Line and Load
<b>FRAME</b>	3
<b>CLASS</b>	Class A
<b>COMMUNICATION</b>	CAM Link
<b>INTERRUPT RATING</b>	65 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	690
<b>SWITCH OFF TECHNIQUE</b>	Electronic
<b>VOLTAGE RATING - MAX</b>	600 V

**INTERRUPT RATING RANGE**

35 kAIC @600V (UL/CSA)  
 15 kAIC Icu/ 7.5 kAIC Ics/  
 31.5 kAIC Icm @690V (IEC)  
 100 kAIC Icu/ 100 kAIC Ics/  
 220 kAIC Icm @240V (IEC)  
 65 kAIC @480V (UL)  
 100 kAIC @240V (UL)  
 50 kAIC Icu/ 40 kAIC Ics/  
 105 kAIC Icm @440V (IEC)  
 70 kAIC Icu/ 53 kAIC Ics/  
 154 kAIC Icm @380-415V  
 (IEC)  
 22 kAIC Icu @250 Vdc  
 30 kAIC Icu/ 15 kAIC Ics/ 63  
 kAIC Icm @525V South  
 Africa (IEC)  
 50 kAIC Icu/ 30 kAIC Ics/  
 105 kAIC Icm @480V Brazil  
 (IEC)

<b>NUMBER OF POLES</b>	Four-pole (100% N)
<b>TRIP RATING</b>	250 A
<b>SPECIAL FEATURES</b>	ZSI / CAM / Relays

