



□□□□□

Eaton PDF34MH400P5MJ

Power Defense Globally Rated 100% UL, Frame 3, Four Pole, 400A-High, 65kA/480V, PXR25 ARMS LSIG w/ Modbus RTU and Relays, Std Line Load Term (PDG3X4TA401H)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDF34MH400P5MJ
UPC	786679435472
PRODUCT LENGTH/DEPTH	109.1 mm
PRODUCT HEIGHT	257.1 mm
PRODUCT WIDTH	182.9 mm
PRODUCT WEIGHT	7.68 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked IEC 60947-2

□□□□	
AMPERAGE RATING	400A High Override
VOLTAGE RATING	600 Vac
TRIP TYPE	T294
CIRCUIT BREAKER TYPE	PD3 Global (100% UL)
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Line and Load
FRAME	3
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	690
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	22 kAIC Icu @250 Vdc 100 kAIC @240V (UL)
NUMBER OF POLES	Four-pole (100% N)
SPECIAL FEATURES	Modbus / relays

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

