



□□□□

Eaton PDF63P2000P4WM

Eaton Power Defense molded case circuit breaker, Globally Rated 100% UL, Frame 6, Three Pole, 2000A, 100kA/480V, PXR25 ARMS LSI w/ Modbus RTU, ZSI and Relays, No Terminals (Metric Tapped Conductors)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDF63P2000P4WM
UPC	786687040453
PRODUCT LENGTH/DEPTH	247.7 mm
PRODUCT HEIGHT	406.4 mm
PRODUCT WIDTH	393.7 mm
PRODUCT WEIGHT	46.266 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	2000 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T292
CIRCUIT BREAKER TYPE	PD6 Global (100% UL)
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	6
CLASS	Class A
COMMUNICATION	Modbus RTU
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	690
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V

INTERRUPT RATING RANGE	200 kAIC Icu/ 100 kAIC Ics/ 440 kAIC Icm @240V (IEC) 100 kAIC Icu/ 50 kAIC Ics/ 220 kAIC Icm @440V (IEC) 100 kAIC @480/277V (UL) 35 kAIC Icu/ 18 kAIC Ics/ 73.5 kAIC Icm @690V (IEC) 65 kAIC @600/347V (UL) 85 kAIC Icu/ 40 kAIC Ics/ 187 kAIC Icm @480V Brazil (IEC) 100 kAIC Icu/ 50 kAIC Ics/ 220 kAIC Icm @380-415V (IEC) 40 kAIC Icu/ 25 kAIC Ics/ 84 kAIC Icm @525V South Africa (IEC) 200 kAIC @240V (UL)
-------------------------------	---

NUMBER OF POLES	Three-pole
SPECIAL FEATURES	ZSI / Modbus / Relays

□□

