

Eaton PDG10F0040VFFJ

Eaton Power Defense Globally Rated, Frame 1, Four Pole (0% N), 40A, 25kA/480V, 50C Cal T-M (Fxd-Fxd) TU , Std Line Load Term (PDG1X4T125)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG10F0040VFFJ
UPC	786689290917
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	1.29 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	40 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600 Vac
PROTECTION	0% Protected Neutral Pole
SERIES	Power Defense
TERMINALS	Standard Line and Load
FRAME	1
CLASS	Class A
CALIBRATION	50C Calibration
INTERRUPT RATING	25 kAIC at 480 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
INTERRUPT RATING RANGE	25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @380-415V (IEC)
	35 kAIC @240V (UL)
	14 kAIC @600V (UL/CSA)
	25 kAIC @480V (UL)
	35 kAIC Icu/ 35 kAIC Ics/ 73.5 kAIC Icm @240V (IEC)
	10 kAIC Icu @250 Vdc
NUMBER OF POLES	Four-pole (0% N)

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	