

Eaton PDG10M0080TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Four Pole (0% N), 80A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG1X4T125)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG10M0080TFFL
UPC	786679992692
PRODUCT LENGTH/DEPTH	75.95 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	2.22 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 UL 489 CSA CCC Marked

AMPERAGE RATING	80 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	0% neutral protection
TERMINALS	Standard Terminals Load Only
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	65 kAIC @480V (UL) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 100 kAIC @240V (UL) 25 kAIC @600V (UL/CSA) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 35 kAIC Icu @125 Vdc 35 kAIC Icu @250 Vdc
NUMBER OF POLES	Four-pole (0% N)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: