

Eaton PDG10M0100VFFJ

Eaton Power Defense Globally Rated, Frame 1, Four Pole (0% N), 100A, 65kA/480V, 50C Cal T-M (Fxd-Fxd) TU , Std Line Load Term (PDG1X4T125)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG10M0100VFFJ
UPC	786689289379
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	1.29 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600 Vac
PROTECTION	0% Protected Neutral Pole
SERIES	Power Defense
TERMINALS	Standard Line and Load
FRAME	1
CLASS	Class A
CALIBRATION	50C Calibration
INTERRUPT RATING	65 kAIC at 480 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
INTERRUPT RATING RANGE	42 kAIC Icu @250 Vdc
	70 kAIC Icu/ 50 kAIC Ics/
	154 kAIC Icm @380-415V (IEC)
	100 kAIC Icu/ 100 kAIC Ics/
	220 kAIC Icm @240V (IEC)
	42 kAIC Icu @125 Vdc
	65 kAIC @480/277V (UL)
	100 kAIC @240V (UL)
	25 kAIC @600/347V (UL)
NUMBER OF POLES	Four-pole (0% N)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: