


Eaton PDG10N0080VFFN

Eaton Power Defense Globally Rated, Frame 1, Four Pole (0% N), 80A, 85kA/480V, 50C Cal T-M (Fxd-Fxd) TU , No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG10N0080VFFN
UPC	786689283124
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	1.29 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	80 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600 Vac
PROTECTION	0% Protected Neutral Pole
SERIES	Power Defense
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
CALIBRATION	50C Calibration
INTERRUPT RATING	85 kAIC at 480 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
INTERRUPT RATING RANGE	70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)
	150 kAIC @240V (UL)
	150 kAIC Icu/ 100 kAIC Ics/ 330 kAIC Icm @240V (IEC)
	35 kAIC Icu/ 25 kAIC Ics/ 73.5 kAIC Icm @525V
	South Africa (IEC)
	65 kAIC Icu/ 40 kAIC Ics/ 143 kAIC Icm @480V Brazil (IEC)
	50 kAIC @600/347V (UL)
	70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @440V (IEC)
	20 kAIC Icu/ 10 kAIC Ics/ 42 kAIC Icm @690V (IEC)
	85 kAIC @480/277V (UL)
NUMBER OF POLES	Four-pole (0% N)



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

