

Eaton PDG11M0020TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Single Pole, 20A, 65kA/480V, T-M (Fxd-Fxd) TU, No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG11M0020TFFN
UPC	786679208656
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	25.4 mm
PRODUCT WEIGHT	0.453592 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked IEC 60947-2 UL 489 CSA

AMPERAGE RATING	20 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	25 kAIC @600V (UL/CSA) 35 kAIC Icu @125 Vdc 35 kAIC Icu @250 Vdc 100 kAIC @240V (UL) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 65 kAIC @480V (UL) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)
NUMBER OF POLES	Single-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.

