



□□□□□

Eaton PDG12C0110TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Two Pole, 110A, 18kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG1X2T125)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG12C0110TFFJ
UPC	786679279137
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	50.8 mm
PRODUCT WEIGHT	0.907 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 UL 489 CSA CCC Marked

□□□□	
AMPERAGE RATING	110 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	1
CLASS	Class A
INTERRUPT RATING	18 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	18 kAIC @480V (UL) 25 kAIC @240V (UL) 25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @240V (IEC) 10 kAIC @600V (UL/CSA) 10 kAIC Icu @125 Vdc 10 kAIC Icu @250 Vdc 20 kAIC Icu/ 20 kAIC Ics/ 42 kAIC Icm @380-415V (IEC)
NUMBER OF POLES	Two-pole

□□

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

