

Eaton PDG13C0080TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 80A, 18kA/480V, T-M (Fxd-Fxd) TU, No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13C0080TFFN
UPC	786679234259
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA UL 489 IEC 60947-2 CCC Marked

AMPERAGE RATING	80 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
INTERRUPT RATING	18 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	10 kAIC @600V (UL/CSA) 20 kAIC Icu/ 20 kAIC Ics/ 42 kAIC Icm @380-415V (IEC) 25 kAIC @240V (UL) 10 kAIC Icu @125 Vdc 18 kAIC @480V (UL) 10 kAIC Icu @250 Vdc 25 kAIC Icu/ 25 kAIC Ics/ 52.5 kAIC Icm @240V (IEC)
NUMBER OF POLES	Three-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

