



□□□□□

Eaton PDG13K0070TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 70A, 50kA/480V, T-M (Fxd-Fxd) TU, No Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13K0070TFFN
UPC	786679282113
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked

□□□□	
AMPERAGE RATING	70A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
INTERRUPT RATING	50 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	35 kAIC Icu @125 Vdc 22 kAIC @600V (UL/CSA) 85 kAIC Icu/ 85 kAIC Ics/ 187 kAIC Icm @240V (IEC) 35 kAIC Icu @250 Vdc 50 kAIC Icu/ 50 kAIC Ics/ 105 kAIC Icm @380-415V (IEC) 85 kAIC @240V (UL) 50 kAIC @480V (UL)
NUMBER OF POLES	Three-pole

□□

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

