

Eaton PDG13K0110TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 110A, 50kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG1X3T125)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13K0110TFFJ
UPC	786679239636
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CSA CCC Marked UL 489

AMPERAGE RATING	110 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	1
CLASS	Class A
INTERRUPT RATING	50 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	22 kAIC @600V (UL/CSA) 35 kAIC Icu @125 Vdc 50 kAIC @480V (UL) 85 kAIC @240V (UL) 35 kAIC Icu @250 Vdc 50 kAIC Icu/ 50 kAIC Ics/ 105 kAIC Icm @380-415V (IEC) 85 kAIC Icu/ 85 kAIC Ics/ 187 kAIC Icm @240V (IEC)
NUMBER OF POLES	Three-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: