

Eaton

PDG13M0003MSAN

Eaton Power Defense motor protection circuit breaker, Globally Rated, Frame 1, Three Pole, 3A, 65kA/480V, Motor protection, Standard Calibration, Adjustable, No Terminals

PRODUCT NAME	Eaton Power Defense motor protection circuit breaker
CATALOG NUMBER	PDG13M0003MSAN
UPC	786679297469
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.25 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 IEC 60947-2 CSA CCC Marked

AMPERAGE RATING	3 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD1 Global
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
MAX. RATED OPERATION VOLTAGE UE AC	600
SWITCH OFF TECHNIQUE	Thermomagnetic
NUMBER OF POLES	Three-pole
TYPE	Motor protection
INTERRUPT RATING RANGE	65 kAIC at 480 V (UL) 100 kAIC at 240 V (UL) 70 kAIC Icu/50 kAIC Ics/154 kAIC Icm at 380-415 V (IEC)
	35 kAIC Icu at 250 Vdc 25 kAIC at 600 V (UL/CSA) 100 kAIC Icu/100 kAIC Ics/220 kAIC Icm at 240 V (IEC) 35 kAIC Icu at 125 Vdc
VOLTAGE RATING - MAX	600 V

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

