

Eaton PDG13M0030VFFN

Eaton Power Defense Globally Rated, Frame 1, Three Pole, 30A, 65kA/480V, 50C Cal T-M (Fxd-Fxd) TU , No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13M0030VFFN
UPC	786689282547
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.04 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	30 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600 Vac
SERIES	Power Defense
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
CALIBRATION	50C Calibration
INTERRUPT RATING	65 kAIC at 480 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
INTERRUPT RATING RANGE	42 kAIC Icu @125 Vdc 42 kAIC Icu @250 Vdc 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 25 kAIC @600/347V (UL) 65 kAIC @480/277V (UL) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 100 kAIC @240V (UL)
NUMBER OF POLES	Three-pole

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

