

## Eaton PDG13M0060VFFJ

Eaton Power Defense Globally Rated, Frame 1, Three Pole, 60A, 65kA/480V, 50C Cal T-M (Fxd-Fxd) TU , Std Line Load Term (PDG1X3T125)

|                             |                                                 |
|-----------------------------|-------------------------------------------------|
|                             |                                                 |
| <b>PRODUCT NAME</b>         | Eaton Power Defense molded case circuit breaker |
| <b>CATALOG NUMBER</b>       | PDG13M0060VFFJ                                  |
| <b>UPC</b>                  | 786689287993                                    |
| <b>PRODUCT LENGTH/DEPTH</b> | 76 mm                                           |
| <b>PRODUCT HEIGHT</b>       | 139.7 mm                                        |
| <b>PRODUCT WIDTH</b>        | 76.2 mm                                         |
| <b>PRODUCT WEIGHT</b>       | 1.04 kg                                         |
| <b>COMPLIANCES</b>          | RoHS Compliant                                  |

|                            |                                                                                                                                                                                                                                                 |
|----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                            |                                                                                                                                                                                                                                                 |
| AMPERAGE RATING            | 60 A                                                                                                                                                                                                                                            |
| VOLTAGE RATING             | 600 Vac                                                                                                                                                                                                                                         |
| TRIP TYPE                  | T298                                                                                                                                                                                                                                            |
| CIRCUIT BREAKER TYPE       | PD1 Global                                                                                                                                                                                                                                      |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker                                                                                                                                                                                                                                |
| VOLTAGE - MAX              | 600 Vac                                                                                                                                                                                                                                         |
| SERIES                     | Power Defense                                                                                                                                                                                                                                   |
| TERMINALS                  | Standard Line and Load                                                                                                                                                                                                                          |
| FRAME                      | 1                                                                                                                                                                                                                                               |
| CLASS                      | Class A                                                                                                                                                                                                                                         |
| CALIBRATION                | 50C Calibration                                                                                                                                                                                                                                 |
| INTERRUPT RATING           | 65 kAIC at 480 Vac                                                                                                                                                                                                                              |
| SWITCH OFF TECHNIQUE       | Thermomagnetic                                                                                                                                                                                                                                  |
| INTERRUPT RATING RANGE     | 42 kAIC Icu @250 Vdc<br>70 kAIC Icu/ 50 kAIC Ics/<br>154 kAIC Icm @380-415V (IEC)<br>100 kAIC Icu/ 100 kAIC Ics/<br>220 kAIC Icm @240V (IEC)<br>65 kAIC @480/277V (UL)<br>100 kAIC @240V (UL)<br>25 kAIC @600/347V (UL)<br>42 kAIC Icu @125 Vdc |
| NUMBER OF POLES            | Three-pole                                                                                                                                                                                                                                      |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: