

Eaton PDG13M0090TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 90A, 65kA/480V, T-M (Fxd-Fxd) TU, No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13M0090TFFN
UPC	786679292426
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 UL 489 CSA CCC Marked

AMPERAGE RATING	90 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 25 kAIC @600V (UL/CSA) 65 kAIC @480V (UL) 100 kAIC @240V (UL) 35 kAIC Icu @125 Vdc 35 kAIC Icu @250 Vdc 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)
NUMBER OF POLES	Three-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: