

Eaton PDG13M0100TFFK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 100A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Line Only (PDG1X3T125)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13M0100TFFK
UPC	786687041504
PRODUCT LENGTH/DEPTH	75.95 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 IEC 60947-2 CCC Marked CSA

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Line Only
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	25 kAIC @600V (UL/CSA)
	100 kAIC @240V (UL)
	65 kAIC @480V (UL)
	35 kAIC Icu @125 Vdc
	70 kAIC Icu/ 50 kAIC Ics/
	154 kAIC Icm @380-415V (IEC)
	35 kAIC Icu @250 Vdc
	100 kAIC Icu/ 100 kAIC Ics/
	220 kAIC Icm @240V (IEC)
NUMBER OF POLES	Three-pole

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	