

Eaton PDG13M0125KNSK

Eaton Power Defense molded case switch, Globally Rated, Frame 1, Three Pole, 125A, 65kA/480V, Molded Case Switch, Standard Terminals Line Only (PDG1X3T125)

PRODUCT NAME	Eaton Power Defense molded case switch
CATALOG NUMBER	PDG13M0125KNSK
UPC	786679906071
PRODUCT LENGTH/DEPTH	75.95 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CSA CCC Marked UL 489

AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Line Only
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
MAX. RATED OPERATION VOLTAGE UE AC	600
SWITCH OFF TECHNIQUE	Thermomagnetic
NUMBER OF POLES	Three-pole
TYPE	Molded case switch
	70 kAIC Icu/50 kAIC Ics/154 kAIC Icm at 380-415 V (IEC)
INTERRUPT RATING RANGE	35 kAIC Icu at 250 Vdc 65 kAIC at 480 V (UL) 25 kAIC at 600 V (UL/CSA) 35 kAIC Icu at 125 Vdc 100 kAIC Icu/100 kAIC Ics/220 kAIC Icm at 240 V (IEC) 100 kAIC at 240 V (UL)
VOLTAGE RATING - MAX	600 V

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	