

Eaton PDG13P0040TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 40A, 100kA/480V, T-M (Fxd-Fxd) TU, No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG13P0040TFFN
UPC	786679292389
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA CCC Marked IEC 60947-2 UL 489

AMPERAGE RATING	40 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
INTERRUPT RATING	100 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	200 kAIC @240V (UL) 200 kAIC Icu/ 150 kAIC Ics/ 440 kAIC Icm @240V (IEC) 35 kAIC @600 (UL/CSA) 100 kAIC @480V (UL) 42 kAIC Icu @250 Vdc 42 kAIC Icu @125 Vdc 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @380-415V (IEC)
NUMBER OF POLES	Three-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: