

Eaton PDG14G0050VFFN

Eaton Power Defense Globally Rated, Frame 1, Four Pole, 50A, 35kA/480V, 50C Cal T-M (Fxd-Fxd) TU , No Terminals

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG14G0050VFFN
UPC	786689286422
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	1.29 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	50 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600 Vac
SERIES	Power Defense
TERMINALS	No Terminals
FRAME	1
CLASS	Class A
CALIBRATION	50C Calibration
INTERRUPT RATING	35 kAIC at 480 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
INTERRUPT RATING RANGE	55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC) 18 kAIC @600V (UL/CSA) 22 kAIC Icu @125 Vdc 36 kAIC Icu/ 36 kAIC Ics/ 76 kAIC Icm @380-415V (IEC) 22 kAIC Icu @250 Vdc 65 kAIC @240V (UL) 35 kAIC @480V (UL)
NUMBER OF POLES	Four-pole

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

