

Eaton PDG14G0125KNSK

Eaton Power Defense molded case switch, Globally Rated, Frame 1, Four Pole (100% N), 125A, 35kA/480V, Molded Case Switch, Standard Terminals Line Only (PDG1X4T125)

PRODUCT NAME	Eaton Power Defense molded case switch
CATALOG NUMBER	PDG14G0125KNSK
UPC	786679860595
PRODUCT LENGTH/DEPTH	75.95 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	2.22 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked CSA IEC 60947-2 UL 489

AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Terminals Line Only
FRAME	1
CLASS	Class A
INTERRUPT RATING	35 kAIC at 480 Vac
MAX. RATED OPERATION VOLTAGE UE AC	600
SWITCH OFF TECHNIQUE	Thermomagnetic
NUMBER OF POLES	Four-pole (100% N)
TYPE	Molded case switch
INTERRUPT RATING RANGE	35 kAIC at 480 V (UL) 55 kAIC Icu/55 kAIC Ics/121 kAIC Icm at 240 V (IEC) 22 kAIC Icu at 125 Vdc 22 kAIC Icu at 250 Vdc 18 kAIC at 600 V (UL/CSA) 36 kAIC Icu/36 kAIC Ics/76 kAIC Icm at 380-415 V (IEC) 65 kAIC at 240 V (UL)
VOLTAGE RATING - MAX	600 V

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

