

Eaton PDG14M0125KNSK

Eaton Power Defense molded case switch, Globally Rated, Frame 1, Four Pole (100% N), 125A, 65kA/480V, Molded Case Switch, Standard Terminals Line Only (PDG1X4T125)

PRODUCT NAME	Eaton Power Defense molded case switch
CATALOG NUMBER	PDG14M0125KNSK
UPC	786679865286
PRODUCT LENGTH/DEPTH	75.95 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	101.6 mm
PRODUCT WEIGHT	2.22 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked

AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD1 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
PROTECTION	100% neutral protection
TERMINALS	Standard Terminals Line Only
FRAME	1
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
MAX. RATED OPERATION VOLTAGE UE AC	600
SWITCH OFF TECHNIQUE	Thermomagnetic
NUMBER OF POLES	Four-pole (100% N)
TYPE	Molded case switch
INTERRUPT RATING RANGE	100 kAIC at 240 V (UL)
	25 kAIC at 600 V (UL/CSA)
	70 kAIC Icu/50 kAIC Ics/154 kAIC Icm at 380-415 V (IEC)
	35 kAIC Icu at 125 Vdc
	100 kAIC Icu/100 kAIC Ics/220 kAIC Icm at 240 V (IEC)
	65 kAIC at 480 V (UL)
	35 kAIC Icu at 250 Vdc
VOLTAGE RATING - MAX	600 V

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	