



□□□□

Eaton PDG21G0150TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Single Pole, 150A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG2X1TA225)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG21G0150TFFJ
UPC	786679217870
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked CSA IEC 60947-2 UL 489



Powering Business Worldwide

□□□□

AMPERAGE RATING	150 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	35 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V

30 kAIC Icu/ 22.5 kAIC Ics/
63 kAIC Icm @440V (IEC)
36 kAIC Icu/ 36 kAIC Ics/
75.6 kAIC Icm @380-415V
(IEC)
18 kAIC @600V (UL/CSA)
55 kAIC Icu/ 55 kAIC Ics/
121 kAIC Icm @240V (IEC)
35 kAIC @480V (UL)

INTERRUPT RATING RANGE

10 kAIC Icu @125 Vdc
20 kAIC Icu/ 15/13 kAIC
Ics/ 42 kAIC Icm @525V
South Africa (IEC)
25 kAIC Icu/ 20 kAIC Ics/
52.5 kAIC Icm @480V
Brazil (IEC)
65 kAIC @240V (UL)
8 kAIC Icu/ 4 kAIC Ics/ 16.8
kAIC Icm @690V (IEC)
10 kAIC Icu @250 Vdc

NUMBER OF POLES	Single-pole
------------------------	-------------

□□

