

# Eaton PDG21M0020VFFK

Eaton Power Defense Globally Rated, Frame 2, Single Pole, 20A, 65kA/480V, 50C Cal T-M (Fxd-Fxd) TU, Std Term Line Only (PDG2X1T100)

|                      |                                                 |
|----------------------|-------------------------------------------------|
|                      |                                                 |
| PRODUCT NAME         | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER       | PDG21M0020VFFK                                  |
| UPC                  | 786689265335                                    |
| PRODUCT LENGTH/DEPTH | 88.9 mm                                         |
| PRODUCT HEIGHT       | 152.4 mm                                        |
| PRODUCT WIDTH        | 35.1 mm                                         |
| PRODUCT WEIGHT       | 2.041 kg                                        |
| COMPLIANCES          | RoHS Compliant                                  |

|                            |                              |
|----------------------------|------------------------------|
|                            |                              |
| AMPERAGE RATING            | 20 A                         |
| VOLTAGE RATING             | 600 Vac                      |
| TRIP TYPE                  | T298                         |
| CIRCUIT BREAKER TYPE       | PD2 Global                   |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker             |
| VOLTAGE - MAX              | 600Vac                       |
| SERIES                     | Power defense                |
| TERMINALS                  | Standard Terminals Line Only |
| FRAME                      | 2                            |
| CLASS                      | Class A                      |
| CALIBRATION                | 50C Calibration              |
| RATING PLUG                | no                           |
| INTERRUPT RATING           | 25 kAIC at 600 Vac           |
| SWITCH OFF TECHNIQUE       | Thermomagnetic               |
| VOLTAGE RATING - MAX       | 600 V                        |
| RATED OPERATIONAL CURRENT  | 20 A                         |
| NUMBER OF POLES            | Single-pole                  |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

