

Eaton PDG21M0020VFFL

Eaton Power Defense Globally Rated, Frame 2, Single Pole, 20A, 65kA/480V, 50C Cal T-M (Fxd-Fxd) TU, Std Term Load Only (PDG2X1T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG21M0020VFFL
UPC	786689265434
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	20 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600Vac
SERIES	Power defense
TERMINALS	Standard Terminals Load Only
FRAME	2
CLASS	Class A
CALIBRATION	50C Calibration
RATING PLUG	no
INTERRUPT RATING	25 kAIC at 600 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
RATED OPERATIONAL CURRENT	20 A
NUMBER OF POLES	Single-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

