

Eaton PDG21M0025TFFK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Single Pole, 25A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Line Only (PDG2X1T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG21M0025TFFK
UPC	786679863985
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CCC Marked CSA UL 489 IEC 60947-2

AMPERAGE RATING	25 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Line Only
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	22 kAIC Icu @125 Vdc
	35 kAIC @600V (UL/CSA)
	65 kAIC @480V (UL)
	10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)
	100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)
	100 kAIC @240V (UL)
	50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)
	22 kAIC Icu @250 Vdc
	30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)
	70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)
	50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC)
NUMBER OF POLES	Single-pole



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

