



□□□□

Eaton PDG21M0050TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Single Pole, 50A, 65kA/480V, T-M (Fxd-Fxd) TU, No Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG21M0050TFFN
UPC	786679259801
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 UL 489 CCC Marked CSA



Powering Business Worldwide

□□□□

AMPERAGE RATING	50 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC) 22 kAIC Icu @250 Vdc 100 kAIC @240V (UL) 70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC) 30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC) 65 kAIC @480V (UL) 35 kAIC @600V (UL/CSA) 100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC) 22 kAIC Icu @125 Vdc 50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)
NUMBER OF POLES	Single-pole

□□

