



□□□□

Eaton PDG21M0060TFFN

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Single Pole, 60A, 65kA/480V, T-M (Fxd-Fxd) TU, No Terminals

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG21M0060TFFN
UPC	786679320747
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	60 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	No Terminals
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V

100 kAIC @240V (UL)
50 kAIC Icu/ 40 kAIC Ics/
105 kAIC Icm @440V (IEC)
22 kAIC Icu @125 Vdc
10 kAIC Icu/ 5 kAIC Ics/ 21
kAIC Icm @690V (IEC)
35 kAIC @600V (UL/CSA)
100 kAIC Icu/ 100 kAIC Ics/
220 kAIC Icm @240V (IEC)
50 kAIC Icu/ 30 kAIC Ics/
105 kAIC Icm @480V Brazil
(IEC)
70 kAIC Icu/ 53 kAIC Ics/
154 kAIC Icm @380-415V
(IEC)
30/25 kAIC Icu/ 15/13 kAIC
Ics @525V South Africa
(IEC)
22 kAIC Icu @250 Vdc
65 kAIC @480V (UL)

INTERRUPT RATING RANGE	
NUMBER OF POLES	Single-pole

□□

