

Eaton PDG21M0070VFFK

Eaton Power Defense Globally Rated, Frame 2, Single Pole, 70A, 65kA/480V, 50C Cal T-M (Fxd-Fxd) TU, Std Term Line Only (PDG2X1T100)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG21M0070VFFK
UPC	786689266264
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	35.1 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	70A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
VOLTAGE - MAX	600Vac
SERIES	Power defense
TERMINALS	Standard Terminals Line Only
FRAME	2
CLASS	Class A
CALIBRATION	50C Calibration
RATING PLUG	no
INTERRUPT RATING	25 kAIC at 600 Vac
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V
RATED OPERATIONAL CURRENT	70 A
NUMBER OF POLES	Single-pole

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

