



□□□□

Eaton PDG22M0100KNSL

Eaton Power Defense molded case switch, Globally Rated, Frame 2, Two Pole, 100A, 65kA/480V, Molded Case Switch, Standard Terminals Load Only (PDG2X2T100)

□□□□

PRODUCT NAME	Eaton Power Defense molded case switch
CATALOG NUMBER	PDG22M0100KNSL
UPC	786679924006
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	69.9 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked



Powering Business Worldwide

□□□□

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Load Only
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
MAX. RATED OPERATION VOLTAGE UE AC	600
SWITCH OFF TECHNIQUE	Thermomagnetic
NUMBER OF POLES	Two-pole
TYPE	Molded case switch
INTERRUPT RATING RANGE	<p>22 kAIC Icu at 250 Vdc 22 kAIC Icu at 125 Vdc 50 kAIC Icu/30 kAIC Ics/105 kAIC Icm at 480 V Brazil (IEC) 35 kAIC at 600 V (UL/CSA) 65 kAIC at 480 V (UL) 10 kAIC Icu/5 kAIC Ics/21 kAIC Icm at 690 V (IEC) 70 kAIC Icu/53 kAIC Ics/154 kAIC Icm at 380-415 V (IEC)</p> <p>100 kAIC Icu/100 kAIC Ics/220 kAIC Icm at 240 V (IEC) 30/25 kAIC Icu/15/13 kAIC Ics at 525 V South Africa (IEC) 100 kAIC at 240 V (UL) 50 kAIC Icu/40 kAIC Ics/105 kAIC Icm at 440 V (IEC)</p>
VOLTAGE RATING - MAX	600 V

□□

