



□□□□

Eaton PDG22M0125TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Two Pole, 125A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG2X2TA225)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG22M0125TFFJ
UPC	786679247518
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	69.9 mm
PRODUCT WEIGHT	2.041 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CSA CCC Marked UL 489



Powering Business Worldwide

□□□□

AMPERAGE RATING	125 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T298
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Thermomagnetic
VOLTAGE RATING - MAX	600 V

70 kAIC Icu/ 53 kAIC Ics/
154 kAIC Icm @380-415V
(IEC)
35 kAIC @600V (UL/CSA)
10 kAIC Icu/ 5 kAIC Ics/ 21
kAIC Icm @690V (IEC)
50 kAIC Icu/ 40 kAIC Ics/
105 kAIC Icm @440V (IEC)
100 kAIC @240V (UL)
INTERRUPT RATING RANGE 100 kAIC Icu/ 100 kAIC Ics/
220 kAIC Icm @240V (IEC)
22 kAIC Icu @250 Vdc
22 kAIC Icu @125 Vdc
30/25 kAIC Icu/ 15/13 kAIC
Ics @525V South Africa
(IEC)
50 kAIC Icu/ 30 kAIC Ics/
105 kAIC Icm @480V Brazil
(IEC)
65 kAIC @480V (UL)

NUMBER OF POLES	Two-pole
------------------------	----------

□□

