



□□□□

Eaton PDG23G0060E3MK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 60A, 35kA/480V, PXR20 LSIG w/ Modbus RTU and Relays, Standard Terminals Line Only (PDG2X3T100)

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG23G0060E3MK |
| UPC | 786679875711 |
| PRODUCT LENGTH/DEPTH | 88.9 mm |
| PRODUCT HEIGHT | 152.4 mm |
| PRODUCT WIDTH | 104.6 mm |
| PRODUCT WEIGHT | 1.82 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | IEC 60947-2 CCC Marked UL 489 CSA |



Powering Business Worldwide

| | |
|---|---|
| AMPERAGE RATING | 60 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T285 |
| CIRCUIT BREAKER TYPE | PD2 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| TERMINALS | Standard Terminals Line Only |
| FRAME | 2 |
| CLASS | Class A |
| COMMUNICATION | Modbus RTU |
| INTERRUPT RATING | 35 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC) 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC) 36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC) 65 kAIC @240V (UL) 20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC) 10 kAIC Icu @250 Vdc 8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC) 10 kAIC Icu @125 Vdc 18 kAIC @600V (UL/CSA) 35 kAIC @480V (UL) 55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC) |
| NUMBER OF POLES | Three-pole |
| TRIP RATING | 60 A |
| SPECIAL FEATURES | Modbus / relays |

