



□□□□

## Eaton PDG23G0100TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 100A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG2X3T100)

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG23G0100TFFJ
<b>UPC</b>	786679250358
<b>PRODUCT LENGTH/DEPTH</b>	88.9 mm
<b>PRODUCT HEIGHT</b>	152.4 mm
<b>PRODUCT WIDTH</b>	104.6 mm
<b>PRODUCT WEIGHT</b>	2.26796185 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA UL 489 CCC Marked IEC 60947-2



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	100 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T298
<b>CIRCUIT BREAKER TYPE</b>	PD2 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>TERMINALS</b>	Standard Line and Load
<b>FRAME</b>	2
<b>CLASS</b>	Class A
<b>INTERRUPT RATING</b>	35 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Thermomagnetic
<b>VOLTAGE RATING - MAX</b>	600 V

18 kAIC @600V (UL/CSA)  
36 kAIC Icu/ 36 kAIC Ics/  
75.6 kAIC Icm @380-415V  
(IEC)  
10 kAIC Icu @250 Vdc  
35 kAIC @480V (UL)  
30 kAIC Icu/ 22.5 kAIC Ics/  
63 kAIC Icm @440V (IEC)  
65 kAIC @240V (UL)  
8 kAIC Icu/ 4 kAIC Ics/ 16.8  
kAIC Icm @690V (IEC)  
55 kAIC Icu/ 55 kAIC Ics/  
121 kAIC Icm @240V (IEC)  
10 kAIC Icu @125 Vdc  
25 kAIC Icu/ 20 kAIC Ics/  
52.5 kAIC Icm @480V  
Brazil (IEC)  
20 kAIC Icu/ 15/13 kAIC  
Ics/ 42 kAIC Icm @525V  
South Africa (IEC)

<b>INTERRUPT RATING RANGE</b>	
<b>NUMBER OF POLES</b>	Three-pole

□□

