



□□□□□

Eaton PDG23M0150B2NJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 150A, 65kA/480V, PXR10 LSI TU, Standard Line and Load (PDG2X3TA225)

□□□□

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23M0150B2NJ
UPC	786679204252
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA IEC 60947-2 UL 489 CCC Marked

□□□□

□□

AMPERAGE RATING	150 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T281
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Line and Load
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	35 kAIC @600V (UL/CSA)
	22 kAIC Icu @250 Vdc
	50 kAIC Icu/ 40 kAIC Ics/
	105 kAIC Icm @440V (IEC)
	65 kAIC @480V (UL)
	22 kAIC Icu @125 Vdc
	50 kAIC Icu/ 30 kAIC Ics/
	105 kAIC Icm @480V Brazil (IEC)
	70 kAIC Icu/ 53 kAIC Ics/
	154 kAIC Icm @380-415V (IEC)
	100 kAIC @240V (UL)
	30/25 kAIC Icu/ 15/13 kAIC
	Ics @525V South Africa (IEC)
	100 kAIC Icu/ 100 kAIC Ics/
	220 kAIC Icm @240V (IEC)
	10 kAIC Icu/ 5 kAIC Ics/ 21
	kAIC Icm @690V (IEC)
	25 kAIC @600V (UL/CSA)
NUMBER OF POLES	Three-pole
SPECIAL FEATURES	None

