


Eaton PDG23M0150B2NL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 150A, 65kA/480V, PXR10 LSI TU, Standard Terminals Load Only (PDG2X3TA225)

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23M0150B2NL
UPC	786679943397
PRODUCT LENGTH/DEPTH	6.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	4.83 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CSA IEC 60947-2 CCC Marked

AMPERAGE RATING	150 A
VOLTAGE RATING	600 Vac
TRIP TYPE	T281
CIRCUIT BREAKER TYPE	PD2 Global
CIRCUIT BREAKER FRAME TYPE	Complete breaker
TERMINALS	Standard Terminals Load Only
FRAME	2
CLASS	Class A
INTERRUPT RATING	65 kAIC at 480 Vac
RATED OPERATION VOLTAGE (UE) AT AC - MAX	600
SWITCH OFF TECHNIQUE	Electronic
VOLTAGE RATING - MAX	600 V
INTERRUPT RATING RANGE	100 kAIC @240V (UL)
	10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)
	35 kAIC @600V (UL/CSA)
	50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC)
	22 kAIC Icu @250 Vdc
	50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)
	30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)
	70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)
	22 kAIC Icu @125 Vdc
	100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)
	65 kAIC @480V (UL)
NUMBER OF POLES	Three-pole
SPECIAL FEATURES	None



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

