



□□□□

## Eaton PDG23M0200TFFJ

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 200A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG2X3TA225)

□□□□

<b>PRODUCT NAME</b>	Eaton Power Defense molded case circuit breaker
<b>CATALOG NUMBER</b>	PDG23M0200TFFJ
<b>UPC</b>	786679237021
<b>PRODUCT LENGTH/DEPTH</b>	88.9 mm
<b>PRODUCT HEIGHT</b>	152.4 mm
<b>PRODUCT WIDTH</b>	104.6 mm
<b>PRODUCT WEIGHT</b>	1.82 kg
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA CCC Marked IEC 60947-2 UL 489



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	200 A
<b>VOLTAGE RATING</b>	600 Vac
<b>TRIP TYPE</b>	T298
<b>CIRCUIT BREAKER TYPE</b>	PD2 Global
<b>CIRCUIT BREAKER FRAME TYPE</b>	Complete breaker
<b>TERMINALS</b>	Standard Line and Load
<b>FRAME</b>	2
<b>CLASS</b>	Class A
<b>INTERRUPT RATING</b>	65 kAIC at 480 Vac
<b>RATED OPERATION VOLTAGE (UE) AT AC - MAX</b>	600
<b>SWITCH OFF TECHNIQUE</b>	Thermomagnetic
<b>VOLTAGE RATING - MAX</b>	600 V

35 kAIC @600V (UL/CSA)  
30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC)  
100 kAIC @240V (UL)  
65 kAIC @480V (UL)  
100 kAIC Icu/ 100 kAIC Ics/ 220 kAIC Icm @240V (IEC)  
22 kAIC Icu @250 Vdc  
10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC)  
22 kAIC Icu @125 Vdc  
50 kAIC Icu/ 30 kAIC Ics/ 105 kAIC Icm @480V Brazil (IEC)  
50 kAIC Icu/ 40 kAIC Ics/ 105 kAIC Icm @440V (IEC)  
70 kAIC Icu/ 53 kAIC Ics/ 154 kAIC Icm @380-415V (IEC)

<b>INTERRUPT RATING RANGE</b>	
<b>NUMBER OF POLES</b>	Three-pole

□□

