



□□□□

Eaton PDG23N0225E2RK

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 225A, 85kA/480V, PXR20 LSI w/ Relays, Standard Terminals Line Only (PDG2X3TA225)

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Power Defense molded case circuit breaker |
| CATALOG NUMBER | PDG23N0225E2RK |
| UPC | 786679968178 |
| PRODUCT LENGTH/DEPTH | 88.9 mm |
| PRODUCT HEIGHT | 152.4 mm |
| PRODUCT WIDTH | 104.6 mm |
| PRODUCT WEIGHT | 1.82 kg |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | CCC Marked CSA IEC 60947-2 UL 489 |



Powering Business Worldwide

□□□□

□□

| | |
|---|--|
| AMPERAGE RATING | 225 A |
| VOLTAGE RATING | 600 Vac |
| TRIP TYPE | T283 |
| CIRCUIT BREAKER TYPE | PD2 Global |
| CIRCUIT BREAKER FRAME TYPE | Complete breaker |
| TERMINALS | Standard Terminals Line Only |
| FRAME | 2 |
| CLASS | Class A |
| INTERRUPT RATING | 85 kAIC at 480 Vac |
| RATED OPERATION VOLTAGE (UE) AT AC - MAX | 600 |
| SWITCH OFF TECHNIQUE | Electronic |
| VOLTAGE RATING - MAX | 600 V |
| INTERRUPT RATING RANGE | 150 kAIC @240V (UL) 70 kAIC Icu/ 70 kAIC Ics/ 154 kAIC Icm @380-415V (IEC) 150 kAIC Icu/ 100 kAIC Ics/ 330 kAIC Icm @240V (IEC) 30/25 kAIC @600V (UL/CSA) 65 kAIC Icu/ 40 kAIC Ics/ 143 kAIC Icm @480V Brazil (IEC) 85 kAIC @480V (UL) 22 kAIC Icu @250 Vdc 10 kAIC Icu/ 5 kAIC Ics/ 21 kAIC Icm @690V (IEC) 22 kAIC Icu @125 Vdc 30/25 kAIC Icu/ 15/13 kAIC Ics @525V South Africa (IEC) 70 kAIC Icu/ 50 kAIC Ics/ 154 kAIC Icm @440V (IEC) 25 kAIC @600V (UL/CSA) |
| NUMBER OF POLES | Three-pole |
| TRIP RATING | 225 A |
| SPECIAL FEATURES | Relays |

